



SG Series Sight Glass

FEATURES AND ADVANTAGES

- Allows for viewing of material flowing through the glass at all times.
- Made of tough Polycarbonate material.
- Supplied with protective caps to cover threads.
- NPT threads allow for connection with an AL-D and AL-A camlocks.

MATERIAL SPECIFICATIONS

- Polycarbonate material.
- NPT Threads.

SERVICE TEMPERATURE RANGE

-50°F (-46°C) to +185°F (+85°C)

VIEW ONLINE



SCAN FOR INFO
or visit
KOA.link/Sight-Glass

Part Number	Size (in)	Length (in)	Wall Thickness (in)	PSI Rating at 70°F	Burst Rating at 70°F	Weight Each (lbs)	Standard Carton
SG200	2	8	0.40	500	2700	0.87	30
SG300	3	8	0.40	500	1900	1.08	12
SG400	4	8	0.40	500	1900	2.25	6

SIGHT GLASS INSTALLATION EXAMPLE



The pictures above show a popular installation set up for the Sight Glass and Funnel Strainer. The picture on the left shows the Funnel Strainer assembled with an aluminum type “D” coupling. The picture on the right shows the complete assembly with the Sight Glass and an aluminum type “A” coupling.

Warning: Never use a wrench on the Sight Glass – always tighten the connecting pieces.

Not for use with hydrocarbons/petroleum products.

Because we continually examine ways to improve our products, we reserve the right to alter specifications or discontinue products without prior notice.