



STBC-CS Series

Standard Duty T-Bolt Clamp

FEATURES AND ADVANTAGES

- T-Bolt design provides extra strength and creates a 360° seal to prevent leaks.
- Hex nut provides easy installation.
- Meets SAE J1508 Type TB

MATERIAL SPECIFICATIONS

- 300 Series stainless steel band.
- Carbon steel plated bolt and nut.

VIEW ONLINE



SCAN FOR INFO
or visit
KOA.link/STBC-CS

Part Number	Size Range (in)	Band Width (in)	Maximum Torque (ft lbs)	Weight Each (lbs)	Standard Carton
STBC-CS131	1 1/4 - 1 1/2	3/4	9	0.06	25
STBC-CS150	1 5/16 - 1 9/16	3/4	9	0.06	25
STBC-CS175	1 9/16 - 1 13/16	3/4	9	0.06	25
STBC-CS188	1 11/16 - 1 15/16	3/4	9	0.07	25
STBC-CS200	1 13/16 - 2 1/16	3/4	9	0.07	25
STBC-CS225	2 1/16 - 2 5/16	3/4	9	0.07	25
STBC-CS238	2 3/16 - 2 1/2	3/4	9	0.08	25
STBC-CS250	2 5/16 - 2 5/8	3/4	9	0.08	25
STBC-CS256	2 13/32 - 2 21/32	3/4	9	0.08	25
STBC-CS263	2 3/8 - 2 11/16	3/4	9	0.08	25
STBC-CS275	2 1/2 - 2 13/16	3/4	9	0.08	25
STBC-CS288	2 5/8 - 2 15/16	3/4	9	0.09	25
STBC-CS300	2 3/4 - 3 1/16	3/4	9	0.09	25
STBC-CS312	2 7/8 - 3 3/16	3/4	9	0.09	25
STBC-CS325	2 15/16 - 3 5/16	3/4	9	0.09	25
STBC-CS350	3 1/4 - 3 9/16	3/4	9	0.09	25
STBC-CS375	3 1/2 - 3 13/16	3/4	9	0.09	25
STBC-CS382	3 9/16 - 3 7/8	3/4	9	0.09	25
STBC-CS400	3 3/4 - 4 1/16	3/4	9	0.09	25
STBC-CS425	3 31/32 - 4 5/16	3/4	9	0.10	25
STBC-CS450	4 1/4 - 4 9/16	3/4	9	0.10	25
STBC-CS475	4 1/2 - 4 13/16	3/4	9	0.10	25
STBC-CS500	4 3/4 - 5 1/16	3/4	9	0.10	25
STBC-CS525	5 - 5 5/16	3/4	9	0.10	25
STBC-CS550	5 1/4 - 5 9/16	3/4	9	0.10	25
STBC-CS575	5 1/2 - 5 13/16	3/4	9	0.11	25
STBC-CS600	5 3/4 - 6 1/16	3/4	9	0.11	25
STBC-CS625	5 15/16 - 6 5/16	3/4	9	0.11	25
STBC-CS650	6 1/4 - 6 9/16	3/4	9	0.11	25
STBC-CS675	6 1/2 - 6 13/16	3/4	9	0.12	25
STBC-CS700	6 3/4 - 7 1/32	3/4	9	0.12	25
STBC-CS750	8 15/16 - 9 13/32	3/4	9	0.12	25

Because we continually examine ways to improve our products, we reserve the right to alter specifications or discontinue products without prior notice.