



STBC-SS Series

Standard Duty T-Bolt Clamp

FEATURES AND ADVANTAGES


- T-Bolt design provides extra strength and creates a 360° seal to prevent leaks.
- Hex nut provides easy installation.
- Meets SAE J1508 Type TB

MATERIAL SPECIFICATIONS

- 300 Series stainless steel band, bolt, and nut.

VIEW ONLINE



 **SCAN FOR INFO**
or visit
KOA.link/STBC-SS

Part Number	Size Range (in)	Band Width (in)	Maximum Torque (ft lbs)	Weight Each (lbs)	Standard Carton
STBC-SS131	1 1/4 - 1 1/2	3/4	9	0.07	25
STBC-SS150	1 5/16 - 1 9/16	3/4	9	0.07	25
STBC-SS163	1 7/16 - 1 11/16	3/4	9	0.07	25
STBC-SS175	1 9/16 - 1 13/16	3/4	9	0.07	25
STBC-SS188	1 11/16 - 1 15/16	3/4	9	0.07	25
STBC-SS200	1 13/16 - 2 1/16	3/4	9	0.07	25
STBC-SS212	1 15/16 - 2 3/16	3/4	9	0.07	25
STBC-SS225	2 1/16 - 2 5/16	3/4	9	0.08	25
STBC-SS238	2 3/16 - 2 1/2	3/4	9	0.08	25
STBC-SS250	2 5/16 - 2 5/8	3/4	9	0.08	25
STBC-SS256	2 13/32 - 2 21/32	3/4	9	0.08	25
STBC-SS263	2 3/8 - 2 11/16	3/4	9	0.08	25
STBC-SS275	2 1/2 - 2 13/16	3/4	9	0.08	25
STBC-SS288	2 5/8 - 2 15/16	3/4	9	0.08	25
STBC-SS300	2 3/4 - 3 1/16	3/4	9	0.09	25
STBC-SS312	2 7/8 - 3 3/16	3/4	9	0.09	25
STBC-SS325	2 15/16 - 3 5/16	3/4	9	0.09	25
STBC-SS350	3 1/4 - 3 9/16	3/4	9	0.09	25
STBC-SS362	3 3/8 - 3 11/16	3/4	9	0.09	25
STBC-SS375	3 1/2 - 3 13/16	3/4	9	0.09	25
STBC-SS382	3 9/16 - 3 7/8	3/4	9	0.09	25
STBC-SS400	3 3/4 - 4 1/16	3/4	9	0.09	25
STBC-SS425	3 31/32 - 4 5/16	3/4	9	0.10	25
STBC-SS450	4 1/4 - 4 9/16	3/4	9	0.10	25
STBC-SS475	4 1/2 - 4 13/16	3/4	9	0.10	25
STBC-SS500	4 3/4 - 5 1/16	3/4	9	0.10	25
STBC-SS525	5 - 5 5/16	3/4	9	0.11	25
STBC-SS550	5 1/4 - 5 9/16	3/4	9	0.11	25

(CONTINUED)

Because we continually examine ways to improve our products, we reserve the right to alter specifications or discontinue products without prior notice.



STBC-SS Series

Standard Duty T-Bolt Clamp

Part Number	Size Range (in)	Band Width (in)	Maximum Torque (ft lbs)	Weight Each (lbs)	Standard Carton
STBC-SS575	5 1/2 - 5 13/16	3/4	9	0.11	25
STBC-SS600	5 3/4 - 6 1/16	3/4	9	0.11	25
STBC-SS625	5 15/16 - 6 5/16	3/4	9	0.11	25
STBC-SS650	6 1/4 - 6 9/16	3/4	9	0.12	25
STBC-SS675	6 1/2 - 6 13/16	3/4	9	0.12	25
STBC-SS700	6 3/4 - 7 1/32	3/4	9	0.12	25
STBC-SS725	7 1/16 - 7 1/4	3/4	9	0.12	25
STBC-SS750	7 1/4 - 7 9/16	3/4	9	0.12	25
STBC-SS800	7 3/4 - 8 1/16	3/4	9	0.13	25
STBC-SS825	7 15/16 - 8 5/16	3/4	9	0.14	25
STBC-SS850	8 1/4 - 8 9/16	3/4	9	0.14	25
STBC-SS888	8 5/8 - 8 15/16	3/4	9	0.14	25
STBC-SS900	8 3/4 - 9 1/16	3/4	9	0.14	25
STBC-SS950	9 1/4 - 9 9/16	3/4	9	0.14	25
STBC-SS1000	9 3/4 - 10 1/16	3/4	9	0.15	25
STBC-SS1050	10 - 10 9/16	3/4	9	0.15	25
STBC-SS1088	10 5/8 - 10 15/16	3/4	9	0.15	25
STBC-SS1200	11 3/4 - 12 1/16	3/4	9	0.16	25
STBC-SS1288	12 5/8 - 12 15/16	3/4	9	0.16	25

Because we continually examine ways to improve our products, we reserve the right to alter specifications or discontinue products without prior notice.