



KSKIVE2 Hydraulic Hose Skiver

DESCRIPTION

A compact, motor driven unit for hoses up to 2". Includes foot pedal, shaving drawer and spots for eight mandrels. Blade on orbital portion of tool can be adjusted to accommodate different sizes hoses, meaning only the internal mandrel must be changed. Internal skive tools have cutting blade attached and must be changed out when switching between different sized hoses.

View Up To Date Info



← SCAN OR VISIT
[KOA.link/
KSKIVE2](https://KOA.link/KSKIVE2)

INCLUDED ACCESSORIES



Electric Foot Pedal



Shavings Drawer

OPTIONAL ACCESSORIES



Mandrel Holder
Stand
MANDSTAND1

Part Number	Hose Capacity (in)		Motor Info	Skiver Size L x W x H (in)	Weight (lbs)
	Internal Skiving	External Skiving			
KSKIVE2	2	2	1.0 HP (230 V) 1 PH 300 RPM	26.6 x 21.1 x 17.2	15

EXTERNAL SKIVING MANDRELS

Part Number	Description
KS-ESMAND-3	External skiving mandrel Ø 3/16"
KS-ESMAND-4	External skiving mandrel Ø 1/4"
KS-ESMAND-5	External skiving mandrel Ø 5/16"
KS-ESMAND-6	External skiving mandrel Ø 3/8"
KS-ESMAND-8	External skiving mandrel Ø 1/2"
KS-ESMAND-10	External skiving mandrel Ø 5/8"
KS-ESMAND-12	External skiving mandrel Ø 3/4"
KS-ESMAND-16	External skiving mandrel Ø 1"
KS-ESMAND-20	External skiving mandrel Ø 1 1/4"
KS-ESMAND-24	External skiving mandrel Ø 1 1/2"
KS-ESMAND-32	External skiving mandrel Ø 2"

INTERNAL SKIVING MANDRELS *with Cutting Blade*

Part Number	Description
KS-ISMAND-8	Internal skiving mandrel Ø 1/2"
KS-ISMAND-10	Internal skiving mandrel Ø 5/8"
KS-ISMAND-12	Internal skiving mandrel Ø 3/4"
KS-ISMAND-16	Internal skiving mandrel Ø 1"
KS-ISMAND-20	Internal skiving mandrel Ø 1 1/4"
KS-ISMAND-24	Internal skiving mandrel Ø 1 1/2"
KS-ISMAND-32	Internal skiving mandrel Ø 2"

Because we continually examine ways to improve our products, we reserve the right to alter specifications or discontinue products without prior notice.