



50 ft. assembled lengths.

300 PSI Yellow Cover Jackhammer Hose Assemblies

General Applications:

- A durable quality hose to tackle the rugged application of jackhammer service

Construction:

- **Tube** – Black EPDM.
- **Reinforcement** – Spiral polyester yarn.
- **Cover** – Yellow abrasion and ozone resistant EPDM.

Service Temperature Range:

-40°F (-40°C) to +212°F (+100°C)

FEATURES AND ADVANTAGES:

- The cover and tube are made of EPDM to resist ozone, heat and cracking while in service.

Oil Resistance:

Class C - limited oil mist.

Branding:

DURA-JACK™ CRIMPED 300 3/4" MADE IN USA

Packaging:

50 ft. boxed length cartons.

Please Note: Coupled assemblies are rated at 150 PSI.



Shipped in 50 ft. length cartons.



Assembled using crimped steel fittings.

Nominal Specifications

Part Number	Color	ID (in)	OD (in)	Working Pressure (psi)	Length (ft)	Weight (lbs/pc)
YLDJCR075X50ABX	Yellow	3/4	1.15	300	50	19

Because we continually examine ways to improve our products, we reserve the right to alter specifications or discontinue products without prior notice.