

DURAJACK™

DJ Series

300 PSI Red Cover Jackhammer Hose Assemblies



View Up To Date Info



◀ SCAN OR VISIT
[KOA.link/
DJ-RD](https://KOA.link/DJ-RD)



GENERAL APPLICATIONS

- A heavy-duty air hose designed for use with pneumatic jackhammers and other air-operated tools in construction, roadwork, and demolition applications.
- Built to withstand rugged handling and severe working conditions, providing excellent flexibility, abrasion resistance, and coupling retention under high air pressure.

CONSTRUCTION

Tube – Black EPDM
Reinforcement – Braided polyester yarn
Cover – Red EPDM

SERVICE TEMPERATURE RANGE

- 40°F (-40°C) to +212°F (+100°C)

BRANDING

KURIYAMA DURAJACK™ JACKHAMMER HOSE CRIMPED DJ-RD075
3/4" ID WP 300 PSI MAX

FEATURES AND ADVANTAGES


- **Super Abrasion Resistance** – Cover and tube are made of EPDM to resist ozone, heat and cracking for demanding applications.
- **Braided-Construction Quality** – Stable under pressure with minimal expansion and twisting.

OIL RESISTANCE

Class C - limited oil mist.

PACKAGING

50 ft. coil lengths individually wrapped

Series Number	Color	ID (in)	ID (mm)	OD (in)	OD (mm)	Max. Working Pressure (psi)	Total Coiled Length (ft)	Packaging	Weight (lbs/pc)
DJ-RD075x50	 Red	3/4	19	1-3/16	30	300 PSI	50	Wrapped Individually	21

Because we continually examine ways to improve our products, we reserve the right to alter specifications or discontinue products without prior notice.