



## GP300™

### GP Series

EPDM Rubber General Purpose Air & Water Hose

#### GENERAL APPLICATIONS

- Air and water service in industrial, construction, and agricultural applications
- Air compressors
- Pneumatic tools
- Spray equipment
- Low-pressure transfer of non-corrosive liquids

#### CONSTRUCTION

Tube – Black EPDM

Reinforcement – Braided polyester yarn

Cover – Black or Red EPDM

#### SERVICE TEMPERATURE RANGE

-40°F (-40°C) to +212°F (+100°C)

#### FEATURES AND ADVANTAGES

- **Durable Construction** – Long-lasting, resistant to wear, ozone, and hydrocarbons.
- **Uniform 300 PSI** – All sizes rated to 300 PSI for safety.
- **Braided-Construction Quality** – Stable under pressure with minimal expansion and twisting.

#### PACKAGING

Maximum 2 pcs. on reel

1/4" – 1 1/2" ID hoses supplied on plastic reels

2" ID hoses supplied on wooden reels

View Up To Date Info



◀ SCAN OR VISIT  
[KOA.link/  
GP](https://koya.link/GP)

#### SAFETY FACTOR

3:1

#### BRANDING

KURIYAMA GP300™ AIR & WATER GP-  
BK ID WP 300 PSI

| Part Number  |  | Color | ID<br>(in) | ID<br>(mm) | OD<br>(in) | OD<br>(mm) | Max. Working<br>Pressure (psi) | Total Reel<br>Length (ft) | Packaging<br>(lengths per reel) | Weight<br>(lbs/ft) |
|--------------|--|-------|------------|------------|------------|------------|--------------------------------|---------------------------|---------------------------------|--------------------|
| GP-BK025X500 |  | Black | 1/4        | 6          | 33/64      | 13.0       | 300                            | 500                       | 1 x 500'                        | 0.101              |
| GP-BK031X500 |  | Black | 5/16       | 8          | 19/32      | 15.0       | 300                            | 500                       | 1 x 500'                        | 0.128              |
| GP-BK038X500 |  | Black | 3/8        | 10         | 22/32      | 17.5       | 300                            | 500                       | 1 x 500'                        | 0.170              |
| GP-BK050X600 |  | Black | 1/2        | 13         | 53/64      | 21.3       | 300                            | 600                       | 2 x 300'                        | 0.229              |
| GP-BK062X600 |  | Black | 5/8        | 16         | 15/16      | 24.0       | 300                            | 600                       | 2 x 300'                        | 0.254              |
| GP-BK075X600 |  | Black | 3/4        | 19         | 1 5/32     | 29.5       | 300                            | 600                       | 2 x 300'                        | 0.397              |
| GP-BK100X600 |  | Black | 1          | 25         | 1 13/32    | 36.0       | 300                            | 600                       | 2 x 300'                        | 0.512              |
| GP-BK125X200 |  | Black | 1 1/4      | 32         | 1 25/32    | 45.2       | 300                            | 200                       | 2 x 100'                        | 0.811              |
| GP-BK150X200 |  | Black | 1 1/2      | 38         | 2 1/8      | 54.0       | 300                            | 200                       | 2 x 100'                        | 1.151              |
| GP-BK200X200 |  | Black | 2          | 51         | 2 19/32    | 66.0       | 300                            | 200                       | 2 x 100'                        | 1.396              |
| GP-RD025X500 |  | Red   | 1/4        | 6          | 33/64      | 13.0       | 300                            | 500                       | 1 x 500'                        | 0.101              |
| GP-RD031X500 |  | Red   | 5/16       | 8          | 19/32      | 15.0       | 300                            | 500                       | 1 x 500'                        | 0.128              |
| GP-RD038X500 |  | Red   | 3/8        | 10         | 22/32      | 17.5       | 300                            | 500                       | 1 x 500'                        | 0.168              |
| GP-RD050X600 |  | Red   | 1/2        | 13         | 53/64      | 21.3       | 300                            | 600                       | 2 x 300'                        | 0.227              |
| GP-RD062X600 |  | Red   | 5/8        | 16         | 15/16      | 24.0       | 300                            | 600                       | 2 x 300'                        | 0.251              |
| GP-RD075X600 |  | Red   | 3/4        | 19         | 1 5/32     | 29.5       | 300                            | 600                       | 2 x 300'                        | 0.395              |
| GP-RD100X600 |  | Red   | 1          | 25         | 1 13/32    | 36.0       | 300                            | 600                       | 2 x 300'                        | 0.507              |
| GP-RD125X200 |  | Red   | 1 1/4      | 32         | 1 25/32    | 45.2       | 300                            | 200                       | 2 x 100'                        | 0.803              |
| GP-RD150X200 |  | Red   | 1 1/2      | 38         | 2 1/8      | 54.0       | 300                            | 200                       | 2 x 100'                        | 1.140              |
| GP-RD200X200 |  | Red   | 2          | 51         | 2 19/32    | 66.0       | 300                            | 200                       | 2 x 100'                        | 1.382              |

Because we continually examine ways to improve our products, we reserve the right to alter specifications or discontinue products without prior notice.