



Vinylflow® EZ-Lite™ VFL Series

General Purpose PVC Water Discharge Hose

GENERAL APPLICATIONS

- Agriculture
- Construction
- Equipment rental

CONSTRUCTION

Spiral homogeneous PVC construction is ideal for construction and agriculture applications, and provides for minimal elongation.

SERVICE TEMPERATURE RANGE

-10°F (-12°C) to +140°F (+60°C)

View Up To Date Info



← SCAN OR VISIT
[KOA.link/
VFL](https://KOA.link/VFL)

FEATURES AND ADVANTAGES

- **Durable PVC Material** – Provides good abrasion, chemical and UV resistance.
- **“EZ” Design** – An easy to handle, lightweight hose for general purpose applications.
- **Smooth PVC Tube** – Provides low friction loss.
- **PVC Cores** – Hoses coiled around durable PVC cores providing for easy unwinding.
- **Compact Design** – Flat hose design rolls up into tight coils for easy storage and transport, takes up less space than other hoses.

Series Number	Size		Hose ID		Wall Thickness (in)	Working Pressure (psi) at 68°F	Burst Pressure (psi) at 68°F	Coil Length (ft)	Weight (lbs/ft)
	(in)	(mm)	(in)	(mm)					
VFL075	3/4	19.1	0.760	19.3	0.054	100	300	300	0.08
VFL100	1	25.4	1.024	26.0	0.051	85	255	300	0.10
VFL125	1 1/4	31.8	1.299	33.0	0.051	85	255	300	0.12
VFL150	1 1/2	38.1	1.614	41.0	0.045	65	195	300	0.14
VFL200	2	50.8	2.087	53.0	0.048	65	195	300/50	0.16
VFL300	3	76.2	3.071	78.0	0.055	60	180	300/50	0.30
VFL400	4	101.6	4.094	104.0	0.056	60	180	300	0.44
VFL600	6	152.4	6.102	155.0	0.061	40	120	300	0.70
VFL800	8	203.2	8.189	208.0	0.073	40	120	300	1.04

NOTE: Longer lengths available by special order.

Because we continually examine ways to improve our products, we reserve the right to alter specifications or discontinue products without prior notice.