



LF---APLX50



LF---ACEX50

LF PVC Hose Assemblies

GENERAL APPLICATIONS

- Agriculture
- Construction
- Contractor
- Industrial
- Rental

CONSTRUCTION

Spiral homogeneous PVC construction is ideal for irrigation and agriculture applications, and provides for minimal elongation.

SERVICE TEMPERATURE RANGE

-10°F (-12°C) to +140°F (+60°C)

FEATURES AND ADVANTAGES

- Smooth Tube – Provides low friction loss.
- Packaging – Individual carton.
- Storage – Hose coils flat for easy storage.

View Up To Date Info



◀ SCAN OR VISIT

[KOA.link/
LF-Assemblies](https://koya.link/LF-Assemblies)

Part Number	Size (in)	Size (mm)	Wall Thickness (in)	Working Pressure (psi) at 68°F	Coil Length (ft)	Weight (ea/lbs)
LF150APLX50	1 1/2	38.1	0.059	70	50	9.00
LF200APLX50	2	50.8	0.063	65	50	13.50
LF300APLX50	3	76.2	0.067	60	50	21.50
LF400APLX50	4	101.6	0.067	50	50	30.00

Hose Ends: Aluminum pin lug couplings male and female

Part Number	Size (in)	Size (mm)	Wall Thickness (in)	Working Pressure (psi) at 68°F	Coil Length (ft)	Weight (ea/lbs)
LF150ACEX50	1 1/2	38.1	0.059	70	50	9.50
LF200ACEX50	2	50.8	0.063	65	50	13.60
LF300ACEX50	3	76.2	0.067	60	50	22.00
LF400ACEX50	4	101.6	0.067	50	50	31.50

Hose Ends: Aluminum camlocks male x female

Because we continually examine ways to improve our products, we reserve the right to alter specifications or discontinue products without prior notice.