

## OPTION 1:

Print out and use the form below for Tigerflex™ Custom Inquiries.

## OPTION 2:

Visit [Tigerflex.com/custom-inquiry/](http://Tigerflex.com/custom-inquiry/) or scan the code to fill out online.



## COMPANY PROFILE

Company Name \_\_\_\_\_ Contact \_\_\_\_\_  
Address \_\_\_\_\_ City \_\_\_\_\_ State \_\_\_\_\_ Zip \_\_\_\_\_  
Phone \_\_\_\_\_ Fax \_\_\_\_\_ E-mail \_\_\_\_\_

## APPLICATION DETAILS

Application \_\_\_\_\_  
\_\_\_\_\_ Indoor  Outdoor   
Material conveyed \_\_\_\_\_ Solid  Liquid  Gas   
Type of fittings to be used \_\_\_\_\_

## HOSE CONSTRUCTION

Hose style:

- Smooth profile (e.g. F series):
- Convoluted profile (e.g. W series):
- Externally reinforced (e.g. GT series):
- Other:  Describe \_\_\_\_\_

Similar to existing Tigerflex™ hose part number(s) (if applicable) \_\_\_\_\_

Flex material \_\_\_\_\_ Flex color \_\_\_\_\_ Food Grade? Yes  No

Helix material \_\_\_\_\_ Helix color \_\_\_\_\_ Food Grade? Yes  No

Yarn reinforcement? Yes  No  Polyurethane liner? Yes  No  Grounding wire? Yes  No

Hose size(s) (ID) \_\_\_\_\_

Required working pressure \_\_\_\_\_ PSI @ 68° F Required vacuum rating \_\_\_\_\_ in/g @ 68° F

Required bending radius \_\_\_\_\_ in Required hose weight \_\_\_\_\_ lbs

Hose Length \_\_\_\_\_ ft Tolerance +/- \_\_\_\_\_ in

Approvals required? \_\_\_\_\_

Other requirements \_\_\_\_\_

## DELIVERY INFORMATION

Estimated annual volume \_\_\_\_\_ Reoccurring? Yes  No  Required ship date \_\_\_\_\_

Special packaging or shipping requirements \_\_\_\_\_

## SUBMIT TO:

Fax: (847) 885-9010 • Email: [customerservice@kuriyama.com](mailto:customerservice@kuriyama.com) • Submission date \_\_\_\_\_

Because we continually examine ways to improve our products, we reserve the right to alter specifications or discontinue products without prior notice.

