



BHYA Series
Female to Male Brass Hydrant Adapter

BCAP Series
Brass Hydrant Cap

FEATURES AND ADVANTAGES

- Designed for use in connection of hoses, nozzles, hydrants, pipes, or other fittings using NST, NPSH, or GHT threads.
- Made of heavy-duty brass material.
- Brass adapters are more durable and heat resistant than aluminum adapters.

MATERIAL SPECIFICATIONS

- Brass ASTM B584, Grade C85700.

VIEW ONLINE



SCAN FOR INFO

or visit

KOA.link/BHYA-BCAP

Part Number	Female Thread (in)	Male Thread (in)	PSI Rating at 70°F	Weight Each (lbs)	Standard Carton
BHYA-24ST12GH	1 1/2 NST	3/4 GHT	300	0.52	100
BHYA-40ST12GH	2 1/2 NST	3/4 GHT	300	1.16	50
BHYA-40ST16SH	2 1/2 NST	1 NPSH	300	1.03	50
BHYA-40ST24SH	2 1/2 NST	1 1/2 NPSH	300	1.00	40
BHYA-40ST32SH	2 1/2 NST	2 NPSH	300	1.07	40
BHYA-24ST24PT	1 1/2 NST	1 1/2 NPT	300	0.60	100
BHYA-40ST12PT	2 1/2 NST	3/4 NPT	300	0.90	50
BHYA-40ST16PT	2 1/2 NST	1 NPT	300	1.02	50
BHYA-40ST24PT	2 1/2 NST	1 1/2 NPT	300	0.91	40
BHYA-40ST32PT	2 1/2 NST	2 NPT	300	1.11	40
BHYA-40ST24ST	2 1/2 NST	1 1/2 NST	300	0.98	40
BHYA-48ST40ST	3 NST	2 1/2 NST	300	1.72	20
BHYA-24SH24ST	1 1/2 NPSH	1 1/2 NST	300	0.60	100
BHYA-48SH40ST	3 NPSH	2 1/2 NST	300	1.42	20
BHYA-24SH24PT	1 1/2 NPSH	1 1/2 NPT	300	0.60	100

Part Number	Size (in)	PSI Rating at 70°F	Weight Each (lbs)	Standard Carton
BCAP-24SH	1 1/2 NPSH	300	0.55	100
BCAP-24ST	1 1/2 NST	300	0.53	100
BCAP-40SH	2 1/2 NPSH	300	1.41	50
BCAP-40ST	2 1/2 NST	300	1.32	50

Because we continually examine ways to improve our products, we reserve the right to alter specifications or discontinue products without prior notice.