

KCS-TF2/E Series



UPDATED

Hose Capacity (in)		Motor Strength (HP)
1 – 2 Wire	2	4
4 SP / 6 SP	2 / 1 1/2	
Industrial	2	
Max opening (mm)	73	

Cutter Size	
L x W x H (in)	25.6 x 27.6 x 16.5
Weight (lbs)	97
Blade Diameter (mm)	250

Part Number	Motor Info
KCS-TF2/E-230/1	4 HP (230 V) 1 PH
KCS-TF2/E-230/3	4 HP (230 V) 3 PH

View Up To Date Info



← SCAN OR VISIT
[KOA.link/
KCS-TF2-E](https://KOA.link/KCS-TF2-E)

DESCRIPTION


A compact, bench mounted unit ideal for cutting 2" four spiral and 1 1/2" six spiral hydraulic hose.

Ideal for use with KC1-H130 series crimpers.


INCLUDED ACCESSORIES



Recessed Blade



Ventilation Port*



Serrated Blade†
BLADE-SER250


* Separate suction device required for fume extraction

† CAUTION: The included Serrated Blade is not recommended for use with hoses with a steel cover and/or containing steel helical reinforcement.


OPTIONAL ACCESSORIES



Centering &
Measuring Device
CENTER-KCS



Smooth Blade
BLADE-SMT250



Diamond Blade
BLADE-DIA250

Because we continually examine ways to improve our products, we reserve the right to alter specifications or discontinue products without prior notice.