

KCS-TF2 Series



Hose Capacity (in)		Motor Strength (HP)
1 – 2 Wire	2	4
4 SP / 6 SP	2 / 1 1/2	
Industrial	2	
Max opening (mm)	75	

Cutter Size	
L x W x H (in)	33.1 x 21.7 x 45.3
Weight (lbs)	290
Blade Diameter (mm)	250

Part Number	Motor Info
KCS-TF2-230/3	4 HP (230 V) 3 PH

DESCRIPTION

A stand alone unit ideal for cutting 2" four spiral and 1 1/2" six spiral hydraulic hose. The blade is recessed inside the base for additional safety.

Suggested for use with KC3-H130 series crimpers.

[View Up To Date Info](#)



◀ SCAN OR VISIT


KOA.link/

KCS-TF2-2303


INCLUDED ACCESSORIES



Enclosed Blade Chamber



Ventilation Port*




Serrated Blade†
BLADE-SER250


* Separate suction device required for fume extraction

† CAUTION: The included Serrated Blade is not recommended for use with hoses with a steel cover and/or containing steel helical reinforcement

OPTIONAL ACCESSORIES




Centering & Measuring Device
CENTER-KCS



Measuring Hose Tray
TRAY-KCS



Stroke Counter
STROKE-KCS



Smooth Blade
BLADE-SMT250



Diamond Blade
BLADE-DIA250

Because we continually examine ways to improve our products, we reserve the right to alter specifications or discontinue products without prior notice.