



## “Cover Guard Slit” CG-SL™ Series

Pre-slit PVC Protection Cover Hose

### GENERAL APPLICATIONS

- Cable and hose bundle protection (MSHA)
- Mine supply line cover protection

### CONSTRUCTION

PVC tube with rigid PVC helix (pre-slit)

### SERVICE TEMPERATURE RANGE

-4°F (-20°C) to +150°F (+65°C)\*

*\*Actual service temperature range is application dependent.*

View Up To Date Info



← SCAN OR VISIT

[KOA.link/  
CG-SL](https://KOA.link/CG-SL)



### FEATURES AND ADVANTAGES

- **MSHA (08) Approved** – Meets U.S. Dept. of Labor Administration requirements for flame-resistance for use in mines for protection of hose bundles. Optional, special order, red or green colored helix also approved.
- **Easy Slide Helix** – Rigid helix design protects hose tube from cover wear, and allows hose to slide easily over rough surfaces. Easy-to-handle.
- **Pre-Slit** – Allows for easy insertion of hose bundles.

Series Number	ID		OD		Standard Length (ft)	Weight (lbs/ft)
	(in)	(mm)	(in)	(mm)		
CG-SL100	1	25.4	1.28	31.9	100	0.14
CG-SL125	1 1/4	31.8	1.51	38.4	100	0.18
CG-SL150	1 1/2	38.1	1.76	45.1	100	0.21
CG-SL200	2	50.8	2.30	58.4	100	0.28
CG-SL250	2 1/2	63.5	2.81	71.3	100	0.39
CG-SL300	3	76.2	3.35	85.0	100	0.45
CG-SL350	3 1/2	88.9	3.83	97.4	100	0.51
CG-SL400	4	102.4	4.39	111.4	100	0.64

### NOTES:

- Service life may vary depending on operating conditions and type of material being conveyed.

### COMPLIANCES (for details see page 87)

**MSHA (08), Phthalate Free (10), RoHS (11)**

Because we continually examine ways to improve our products, we reserve the right to alter specifications or discontinue products without prior notice.